

KOENIGSEGG SPEEDS AHEAD WITH DIMENSION

Dimension 3D Printer Helps Koenigsegg Develop Supercar with a Torque of 920nm

“Simply put, our Dimension 3D Printer saves time, money and allows us to work more freely”.

— Christian von Koenigsegg, CEO

The Koenigsegg CCXR, the first green supercar.



Real Challenge

Manufacturing and assembling each of the components of a Koenigsegg car is very labour intensive as more than 300 carbonfibre parts make up each high-tech supercar. The best method of designing a new car is to test the parts virtually and as true-to-life prototypes. By testing throughout the development cycle, Koenigsegg's designers can determine which designs yield the best possible results. The team of six starts the development process by designing each individual part on its CAD system. They then 'print' a high density plastic model of each component to carry out various testing scenarios. If changes to the part are required, they can be made manually and then scanned from the altered model component. This scan is then used to make a new CAD model, which can be printed again for further testing.

Previously, Koenigsegg outsourced the 3D printing of its prototypes to a service bureau. This stop/start approach proved to be disruptive to the process and typically added on days to the cycle, halting the development of the car. It also added to the cost and administration of the development process, which reduced Koenigsegg's overall efficiency. The company needed to speed up its prototyping in order to evaluate different versions of a design more quickly and effectively.

Real Solution

Koenigsegg realised that having a 3D printer onsite would speed up the prototyping process and therefore the development of its cars. After evaluating all printers available on the market and judging each one on performance, available materials, price and size, Koenigsegg purchased a Dimension SST 1200es printer.

“Dimension was an obvious choice for us as it not only allows us to modify and print prototypes quickly but also provides us with the option to use them as end use parts in our cars,” said Christian von Koenigsegg, founder and CEO at Koenigsegg Automotive AB. “Once the Dimension printer was up and running, our engineers started using the machine straight away. The benefits were clear immediately. The process of printing prototypes onsite and testing each component has sped up the development of the car design by an estimated 20%.”

How Did Dimension Compare to Traditional Prototyping Methods for Koenigsegg?

Cost	40% saved
Time	20% saved

Real Benefits

The Dimension SST 1200es is now being used in-house for design prototyping of the supercars as first planned. The printer can be used by Koenigsegg for everything from printing engine parts to interior fixtures, for design. It can also be used for tooling, fixtures and studies and on component mountability and serviceability. A key benefit of the Dimension printer is that the prototype parts produced can also be used as working parts in the end product.

“Since purchasing the Dimension printer, the turnaround time for getting a component right in terms of design has decreased enormously, it now only takes a few days instead of a number of weeks,” said Christian von Koenigsegg. “Our designers and engineers can quickly establish a part’s suitability for the supercar without stifling their creative flow.”

The Dimension 3D Printer has aided in the design of Koenigsegg’s latest model, the Agera. Every engineer now has access to the printer, which has not only sped up the design process and allowed the team to be more creative and push the boundaries of supercar development. For example, printing and testing prototypes for the air inlets assisted Koenigsegg’s engineers in developing a supercar with a staggering torque of 920nm reached at 5000rpm.

Christian von Koenigsegg, sums up the impact of the Dimension, “Simply put, it saves time, money and allows us to work more freely.”



Christian Von Koenigsegg, CEO at Koenigsegg with one of the supercars.



Front bumper drill fixture used to test the design.



Mounting the label fixture onto the CCX series.

Stratasys | www.stratasys.com | info@stratasys.com

7665 Commerce Way
Eden Prairie, MN 55344
+1 888 480 3548 (US Toll Free)
+1 952 937 3000 (Intl)
+1 952 937 0070 (Fax)

2 Holtzman St.,
Science Park, PO Box 2496
Rehovot 76124, Israel
+972 74 745-4000
+972 74 745-5000 (Fax)

ISO 9001:2008 Certified

©2013 Stratasys Inc. All rights reserved. Stratasys, Fortus, Dimension, uPrint and FDM are registered trademarks and Fused Deposition Modeling, FDM Technology are trademarks of Stratasys Inc., registered in the United States and other countries. All other trademarks are the property of their respective owners. Product specifications subject to change without notice. Printed in the USA. SSYS-CS-Dimension-Koenigsegg-08-13

For more information about Stratasys systems, materials and applications, call **888.480.3548** or visit www.stratasys.com

