

BREATHING EASIER ON THE TRACK



FDM Carbon Monoxide Filter Takes the Heat

"We are now very comfortable producing quality production parts using our Fortus system."

— Brian Levy, design engineer,
Joe Gibbs Racing

Joe Gibbs Racing places an FDM filter housing on each of its three cars, each time they race.

When it comes to safety, the Joe Gibbs Racing (JGR) design engineers don't leave anything to chance. Thanks to a new SR-100 soluble support material used with Fused Deposition Modeling® (FDM) from Stratasys, they can now create complex carbon monoxide filter housings for their cars using polycarbonate (PC) material, which has a higher temperature rating than the previous material used.

"We are now very comfortable producing quality production parts using our Fortus system," said Brian Levy, JGR design engineer. "We don't worry about them melting or failing during a race."

Joe Gibbs Racing is a premier NASCAR organization with three sponsored cars. Its engineers design and develop parts to enhance the performance of these cars, while maintaining the highest possible safety standards for the drivers. Using FDM to accelerate product development, they create concept models, functional prototypes, manufacturing tools and even end-use parts right in their North Carolina facility. The filter housing is the newest part.

A Safer Car

Each JGR vehicle contains a filter mounted in line with the driver's air conditioning unit that helps clean the air blown into the driver's helmet. "The filter reduces carbon monoxide levels to make the environment safer for our drivers," said Levy. The housing sits close to the car's floor and exhaust system, where it's exposed to temperatures as high as 200 F.

The filter itself is housed in a two-piece assembly that snaps together permanently, making it single-use. "We designed it this way so we don't have to worry about reliability," said Levy. "Any other fastening method would make us less confident in our design." In addition to high temperatures, the housings must withstand the vibration of a speeding race car.

How does FDM compare with traditional tooling for Joe Gibbs Racing?

Method	Cost Per Housing	Lead Time
Conventional fabricating	\$700	6 hours
FDM Technology	\$50	3 hours
SAVINGS	\$650 (93%)	3 hours (50%)

Design Freedom


Because the SR-100 support material washes away from the part after it has been built, design engineers have the freedom to make the part as complex as they want. In the past, JGR was hesitant to produce the part with FDM because, while PC offered strength and heat resistance, no soluble support material was available for use with PC. Supports were broken away by hand, making it difficult to clean cavities, especially on parts with complex geometries, like the filter housing.

“The complex design of the part makes it ideal for an FDM application,” said Levy. “To design these parts to work the way we want them to, we need complex geometry. If we tried to machine the part, we would be forced to sacrifice some of its performance to satisfy machining constraints.”

In addition, Levy and his colleagues want to take some of the load off the CNC department. “Anything we can do to take work off of their plate and find other manufacturing processes is a big help,” Levy said. “This is one of our higher-quantity parts. We produce over 200 a year for all of the race teams. That would be a large order for our CNC department.”



JGR engineers can now build carbon monoxide filters out of polycarbonate, which withstands high temperatures.



Because SR-100 support material washes away, complex geometries pose no problem.

Stratasys | www.stratasys.com | info@stratasys.com

7665 Commerce Way
Eden Prairie, MN 55344
+1 888 480 3548 (US Toll Free)
+1 952 937 3000 (Intl)
+1 952 937 0070 (Fax)

2 Holtzman St.,
Science Park, PO Box 2496
Rehovot 76124, Israel
+972 74 745-4000
+972 74 745-5000 (Fax)

ISO 9001:2008 Certified

©2013 Stratasys Inc. All rights reserved. Stratasys, Fortus, Dimension, uPrint and FDM are registered trademarks and Fused Deposition Modeling, FDM Technology are trademarks of Stratasys Inc., registered in the United States and other countries. All other trademarks are the property of their respective owners. Product specifications subject to change without notice. Printed in the USA. SSYS-CS-Fortus-JGR-SR-08-13

For more information about Stratasys systems, materials and applications, call **888.480.3548** or visit www.stratasys.com

