



Objet30 Pro

Big performance with a small footprint.

The Objet30 Pro™ combines the accuracy and versatility of a high-end rapid prototyping machine with the small footprint of a desktop 3D printer. With a tray size of 300 x 200 x 150 mm (11.81 x 7.87 x 5.9 in.) and print resolution among the finest in the industry, the Objet30 Pro is ideal for prototyping consumer goods, consumer electronics, medical devices and more.

Turn your vision into reality with eight 3D printing materials:

The Objet30 Pro features four Rigid Opaque materials, and specialized photopolymers, including transparent, high-temperature and two simulated polypropylene options. It gives you the power to create realistic models with specialized properties quickly and easily in-house.



LEARN MORE ABOUT THE OBJET30 PRO AT STRATASYS.COM

stratasys

THE 3D PRINTING SOLUTIONS COMPANY™



Objet30 Pro

Driven by powerful PolyJet™ technology

Proven PolyJet 3D Printing is famous for smooth surfaces, fine precision and diverse material properties. It works a bit like inkjet document printing, but instead of jetting drops of ink onto paper, the print head jets microscopic layers of liquid photopolymer onto a build tray and instantly cures them with UV light. The fine layers build up to create a prototype or production part.

Along with the selected model material, the 3D printer features two support material options: SUP705, a gel-like support material designed to uphold overhangs and easily removed with a WaterJet; and SUP706, which is easily removed and soluble for automated post-processing and increased geometric freedom to print complex and delicate features and small cavities.

With its astonishingly realistic aesthetics and ability to deliver special properties such as transparency, flexibility and even biocompatibility, PolyJet 3D Printing offers a competitive edge in consumer products prototyping, precision tooling and specialized production parts.

3D PRINTER SPECIFICATIONS

Model Materials	Rigid Opaque: VeroWhitePlus™, VeroBlackPlus™, VeroGray™, VeroBlue™ Transparent: VeroClear™ Simulated Polypropylene: Rigur™ and Durus™ High Temperature
Support Material	SUP705 (WaterJet removable) SUP706 (soluble)
Maximum Build Size (XYZ)	294 x 192 x 148.6 mm (11.57 x 7.55 x 5.85 in.)
System Size and Weight	82.6 x 60 x 62 cm (32.5 x 23.6 x 24.4 in.); 106 kg (234 lbs.)
Resolution	X-axis: 600 dpi; Y-axis: 600 dpi; Z-axis: 900 dpi
Accuracy	0.1 mm (0.0039 in.) varies depending on part geometry, size, orientation, material and post-processing method
Minimum Layer Thickness	28 microns (0.0011 in.); 16 microns for VeroClear material (.0006 in.)
Build Modes	High quality: 16-micron (.0006 in.) resolution High speed: 30-micron (.001 in.) resolution
Software	Objet Studio™ intuitive 3D printing software
Workstation Compatibility	Windows XP/Windows 7/Windows 8
Network Connectivity	Ethernet TCP/IP 10/100 base T
Operating Conditions	Temperature 18-25°C (64-77°F); relative humidity 30-70%
Power Requirements	Single phase: 100-120V; 50-60Hz; 7A or 200-240V; 50-60Hz 3.5A
Regulatory Compliance	CE, FCC/RoHS



E info@stratasys.com / STRATASYS.COM
ISO 9001:2008 Certified

HEADQUARTERS

7665 Commerce Way, Eden Prairie, MN 55344
+1 888 480-3548 (US Toll Free)
+1 952 937-3000 (Intl)
+1 952 937-0070 (Fax)

2 Holtzman St., Science Park, PO Box 2496
Rehovot 76124, Israel
+972 74 745-4000
+972 74 745-5000 (Fax)