

PPSF

Production-Grade Thermoplastic for Fortus 3D Production Systems



PPSF/PPSU (polyphenylsulfone) material has the excellent heat and chemical resistance – ideal for aerospace, automotive and medical applications. PPSF parts manufactured on Fortus® 3D Production Systems are not only mechanically superior, but also dimensionally accurate, to better predict end-product performance. Users can also sterilize PPSF via steam autoclave, EtO sterilization, plasma sterilization, chemical sterilization and radiation*. PPSF gives you the ability to manufacture parts direct from digital files that are ideal for conceptual modeling, functional prototyping, manufacturing tools and end-use-parts.

Mechanical Properties ¹	Test Method	English	Metric
Tensile Strength (Type 1, 0.125", 0.2"/min)	ASTM D638	8,000 psi	55 MPa
Tensile Modulus (Type 1, 0.125", 0.2"/min)	ASTM D638	300,000 psi	2,100 MPa
Tensile Elongation (Type 1, 0.125", 0.2"/min)	ASTM D638	3%	3%
Flexural Strength (Method 1, 0.05"/min)	ASTM D790	15,900 psi	110 MPa
Flexural Modulus (Method 1, 0.05"/min)	ASTM D790	320,000 psi	2,200 MPa
IZOD Impact, notched (Method A, 23°C)	ASTM D256	1.1 ft-lb/in	58.7 J/m
IZOD Impact, un-notched (Method A, 23°C)	ASTM D256	3.1 ft-lb/in	165.5 J/m

Thermal Properties ³	Test Method	English	Metric
Heat Deflection (HDT) @ 264 psi	ASTM D648	372°F	189°C
Glass Transition Temperature (Tg)	DMA (SSYS)	446°F	230°C
Coefficient of Thermal Expansion	ASTM D696	3.1 ⁻⁰⁵ in/in/°F	5.5 ⁻⁰⁵ mm/mm/°C
Melting Point	-----	Not Applicable ²	Not Applicable ²

Electrical Properties ⁴	Test Method	Value Range
Volume Resistivity	ASTM D257	1.5x10 ¹⁴ - 5.0x10 ¹³ ohms
Dielectric Constant	ASTM D150-98	3.2 - 3.0
Dissipation Factor	ASTM D150-98	.0015 - .0011
Dielectric Strength	ASTM D149-09, Method A	290 - 80 V/mil



Environmental Resistance ⁵	24 hours @ 23°C (73°F)	24 hours @ 100°C (212°F)
Antifreeze (Prestone), 50%	Passed	Passed
Gasoline-Unleaded	Passed	Not tested
Motor Oil 10W-40	Passed	Passed
Power Steering Fluid	Passed	Passed
Transmission Fluid	Passed	Passed
Windshield Washer Fluid, 50%	Passed	Not tested

Other ³	Test Method	Value
Specific Gravity	ASTM D792	1.28
Flame Classification	UL 94	V-0
Rockwell Hardness	ASTM D785	M86
UL File Number	-----	E345258

System Availability	Layer Thickness Capability	Support Structure	Available Colors
Fortus 400mc™	0.013 inch (0.330 mm)	Breakaway	■ Tan
Fortus 900mc™	0.010 inch (0.254 mm) ⁶		

The information presented are typical values intended for reference and comparison purposes only. They should not be used for design specifications or quality control purposes. End-use material performance can be impacted (+/-) by, but not limited to, part design, end-use conditions, test conditions, etc. Actual values will vary with build conditions. Tested parts were built on Fortus 400mc @ 0.010" (0.254 mm) slice. Product specifications are subject to change without notice.

The performance characteristics of these materials may vary according to application, operating conditions, or end use. Each user is responsible for determining that the Stratasys material is safe, lawful, and technically suitable for the intended application, as well as for identifying the proper disposal (or recycling) method consistent with applicable environmental laws and regulations. Stratasys makes no warranties of any kind, express or implied, including, but not limited to, the warranties of merchantability, fitness for a particular use, or warranty against patent infringement.

*Stratasys has not done any sterilization testing on PPSF.

¹ Build orientation is on side long edge.

² Due to amorphous nature, material does not display a melting point.

³ Literature value unless otherwise noted.

⁴ All Electrical Property values were generated from the average of test plaques built with default part density (solid). Test plaques were 4.0 x 4.0 x 0.1 inches (102 x 102 x 2.5 mm) and were built both in the flat and vertical orientation. The range of values is mostly the result of the difference in properties of test plaques built in the flat vs. vertical orientation.

⁵ Test results based on Stress Crack Resistance (24-hour immersion @ 23°C and @ 100°C).

⁶ 0.013 inch (0.330 mm) layer thickness not available on Fortus 900mc.

Stratasys | www.stratasys.com | info@stratasys.com

7665 Commerce Way
Eden Prairie, MN 55344

+1 888 480-3548 (US Toll Free)

+1 952 937-3000 (Intl)

+1 952 937-0070 (Fax)

2 Holtzman St.,
Science Park, PO Box 2496
Rehovot 76124, Israel
+972 74 745-4000
+972 74 745-5000 (Fax)

©2014, 2013 Stratasys Inc. All rights reserved. Stratasys, FDM, Fortus and Finishing Touch are registered trademarks of Stratasys Inc. FDM Technology, Fused Deposition Modeling, Fortus 200mc, Fortus 250mc, Fortus 360mc, Fortus 380mc, Fortus 400mc, Fortus 450mc, Fortus 900mc, Insight, Control Center, Smart Supports, SR-30, SR-100, ABSplus, ABS-ESD7, and TouchWorks are trademarks of Stratasys, Inc. *ULTEM is a trademark of SABIC Innovative Plastics IP BV. All other trademarks are the property of their respective owners, and Stratasys assumes no responsibility with regard to the selection, performance, or use of these non-Stratasys products. Product specifications subject to change without notice. Printed in the USA. FortusPPSFMaterialSpecSheet-US-0914

At the core: Advanced FDM Technology

Fortus systems are based on Stratasys® FDM (fused deposition modeling) technology. FDM is the industry's leading additive manufacturing technology, and the only one that uses production-grade thermoplastics, enabling the most durable parts.

Fortus systems use a wide range of thermoplastics with advanced mechanical properties so your parts can endure high heat, caustic chemicals, sterilization and high-impact applications.

No special facilities needed

You can install a Fortus 3D Production System just about anywhere. No special venting is required because Fortus systems don't produce noxious fumes, chemicals or waste.

No special skills needed

Fortus 3D Production Systems are easy to operate and maintain compared to other additive fabrication systems because there are no messy powders to handle and contain. They're so simple, an operator can be trained to operate a Fortus system in less than 30 minutes.

Get your benchmark on the future of manufacturing

Fine details. Smooth surface finishes. Accuracy. Strength. The best way to see the advantages of a Fortus 3D Production System is to have your own part built on a Fortus system. Get your free part at: stratasys.com.