

Fortus[®] 900mc[™]



Designed and built for size, throughput, precision and repeatability.

The Fortus 900mc, the most precise and largest of the Performance family, was specifically designed for digital manufacturing. Not only was the build envelope dramatically increased in size over previous Fortus systems, there are significant upgrades in its mechanical, electromechanical and electrical systems. Specifically, the head gantry is driven by ball-screw technology resulting in more accurate parts with improvements in predictability and repeatability. Additionally, the control software has been modified to leverage the system's hardware advancements. These features deliver greater throughput, accuracy, repeatability and reliability.

Like all Fortus 3D Production Systems, the Fortus 900mc uses stable thermoplastics that continue to outperform nearly all competing technologies in accuracy and repeatability. Proven FDM technology manufactures parts in production-grade thermoplastics that are ideal for conceptual modeling, functional prototyping, manufacturing tools and end-use parts.

**Learn more about the
Fortus 900mc at
[stratasys.com](https://www.stratasys.com)**



System Specifications

BASE SYSTEM CONFIGURATION											
Build Envelope (XYZ)	36 x 24 x 36 inch (914.4 x 609.6 x 914.4 mm) Platen supports two build zones for either a small or large build sheet										
Material Delivery	Two build material canisters 92 in ³ (1508 cc) Two support material canisters 92 in ³ (1508 cc) Auto changeover between canisters										
MATERIAL OPTIONS											
Layer Thickness:	ASA	ABS [™]	ABS-M30 [™]	ABS-M30i [™]	ABS-ESD7 [™]	PC-ABS	PC-ISO [™]	PC	ULTEM [®] 9085 resin	PPSF	NYLON 12
0.013 inch (0.330 mm)	X	X	X	X		X	X	X	X		X
0.010 inch (0.254 mm)	X	X	X	X	X	X	X	X	X	X	X
0.007 inch (0.178 mm)	X	X	X	X	X	X		X			X
Support Structure:	Soluble	Soluble	Soluble	Soluble	Soluble	Soluble	BASS	BASS, Soluble	BASS	BASS	Soluble
Available Colors:											
OTHER SPECIFICATIONS											
System Size/Weight	109.1 x 66.3 x 79.8 inches (2772 x 1683 x 2027 mm)										
System Size with Manufacturing Light Tower	109.1 x 66.3 x 89.8 inches (2772 x 1683 x 2281 mm)										
Achievable Accuracy	Parts are produced within an accuracy of +/- .0035 inch or +/- .0015 inch per inch whichever is greater (+/- .089 mm or +/- .0371 mm per mm whichever is greater)* <i>+Note: Accuracy is geometry-dependent. Achievable accuracy specification derived from statistical data at 95% dimensional yield. See Fortus 900mc accuracy white paper for more information.</i>										
Network Communication	10/100 base T connection. Ethernet protocol.										
Operator Attendance	Limited attendance for job start and stop required.										
Operating Environment¹	Maximum room temperature of 85°F (29°C). Maximum room humidity of 80%										
Power Requirements¹	230 VAC (three phase) 50/60Hz, Voltage fluctuation +/- Current 40A										
Additional Requirements¹	Compressed Air Required										
Regulatory Compliance¹	CE										
Software	All Fortus systems include Insight [™] and Control Center [™] job processing and management software.										

¹See Fortus 900mc Site Prep Guide for detailed power and environmental specs

Stratasys | www.stratasys.com | info@stratasys.com

7665 Commerce Way
Eden Prairie, MN 55344
+1 888 480-3548 (US Toll Free)
+1 952 937-3000 (Intl)
+1 952 937-0070 (Fax)

2 Holtzman St.
Science Park, PO Box 2496
Rehovot 76124, Israel
+972 74 745-4000
+972 74 745-5000 (Fax)

©2014 Stratasys Ltd. All rights reserved. Stratasys, FDM, Fortus, Fortus 900mc, ABSi, ABS-M30, ABS-M30i, ABS-ESD7, PC-ISO, Insight, Control Center, Stratasys logo, Objet, For a 3D World, Objet Studio, Eden, Eden260, Eden260V, Eden350, Eden350V, Eden500V, Objet500 Connex1, Objet500 Connex2, Objet500 Connex3, Connex, Objet260 Connex, Connex350, Connex500, Objet1000, TangoBlack, TangoGray, TangoPlus, TangoBlackPlus, VeroBlue, VeroBlack, VeroBlackPlus, VeroClear, VeroDent, VeroGray, VeroWhite, VeroWhitePlus, Durus, Endur, Digital Materials, Digital ABS and PolyJet are trademarks or registered trademarks of Stratasys Ltd. and/or its subsidiaries or affiliates and may be registered in certain jurisdictions. ULTEM is a registered trademark of SABIC or affiliates. All other trademarks belong to their respective owners. Fortus900mcSpecSheet-11-14

At the core: Advanced FDM[®] technology

Fortus systems are based on Stratasys FDM technology. FDM builds parts in production-grade thermoplastics, enabling the most durable parts.

Fortus systems use a wide range of thermoplastics with advanced mechanical properties so your parts can endure high heat, caustic chemicals, sterilization and high-impact applications.

No special facilities needed

You can install a Fortus 3D Production System just about anywhere. No special venting is required because Fortus systems produce no noxious fumes, chemicals or waste.

No special skills needed

Compared to other additive fabrication systems, Fortus 3D Production Systems are easy to operate and maintain as there are no messy powders to handle and contain. They're so simple, an operator can be trained to operate a Fortus system in less than 30 minutes.

Get your benchmark on the future of manufacturing

Fine details. Smooth surface finishes. Accuracy. Strength. The best way to see the advantages of a Fortus 3D Production System is to have your own part built on a Fortus system. Get your free part at: stratasys.com